

### Description HE4873

It is a fully formulated compound for physical foamed data cable insulation. HE4873 is a high-density polyethylene compound containing blowing agent for the production of foam or foam-skin insulation.

## **Applications**

**HE4873** is designed to use as physically foamed insulation for:

Data cables

# **Specifications**

**HE4873** meets the following material classification:

ISO 1872-PE, KEGHN, 45-D045 ASTM D1248 Type III, Class A, Category 3, Grade E1, E3

The following cable material standards are met by HE4873:

EN 50290-2-23 <sup>1</sup>

Cables manufactured with HE4873 using sound extrusion practice normally comply with the following cable product standards:

IEC 61156 EN 50288

# **Special Features**

HE4873 consists of specially selected components to offer:

Optimal cell structure Smooth surface Low plate out Easy extrusion High process control Improved crushability



<sup>&</sup>lt;sup>1</sup> Appropriate parts



# **Physical Properties**

Property	Typical Value Data should not be used for	Test Method specification work	
Density Bulk density	946 kg/m³ 500 - 600 kg/m³	ISO 1183-1, Method A	
Melt Flow Rate (140 °C/5 kg)	3,8 g/10min	ISO 1133-1, Method A	
Tensile Strain at Break	600 %	ISO 527-2	
Tensile Strength	23 MPa	ISO 527-2	
Brittleness temperature	< -76 °C	ASTM D 746	
Hardness, Shore D (1 s)	61	ISO 868	

# **Processing Techniques**

HE4873 can be processed over a wide range of conditions. The construction, extruder size and setup of gas injection system all play important roles for selection of proper processing conditions including the extruder temperature profile.

At the gas injection point, a temperature of approximately 185-190°C is recommended for optimal activation of the cell nucleating agent, which is of the exothermic type. Specific recommendations for processing conditions can be determined only when the application and type of equipment are known.

#### Tooling

Pressure tooling is invariably required. The die diameter is a function of the level of expansion with a greater expansion requiring a smaller die. Typically die diameters 20 to 25% below the nominal insulation outer diameter are used.

### Typical extrusion temperatures

Screw cooling	120°C
Zone 1	165°C
Zone 2	180°C
Zone 3	185°C
Gas Injection	
Zone 4	175°C
Zone 5	170°C
Flange	190°C
Adapter	200°C
Head	200°C
Die	220°C

Please contact your local Borealis representative for specific assistance.

BOREALIS



# **Packaging**

Package: Bags

Bulk Octabins

### Storage

**HE4873** should be stored in dry conditions at temperatures below 50°C and protected from UV-light. **Safety** 

The product is not classified as dangerous. Check and follow local codes and regulations!

Please see our "Safety data sheet" / "Product safety information sheet" for details on various aspects of safety, recovery and disposal of the product. For more information, contact your Borealis representative.

### **Disclaimer**

The product(s) mentioned herein are not intended to be used for medical, pharmaceutical or healthcare applications and we do not support their use for such applications.

To the best of our knowledge, the information contained herein is accurate and reliable as of the date of publication; however we do not assume any liability whatsoever for the accuracy and completeness of such information.

Borealis makes no warranties which extend beyond the description contained herein. Nothing herein shall constitute any warranty of merchantability or fitness for a particular purpose.

It is the customer's responsibility to inspect and test our products in order to satisfy itself as to the suitability of the products for the customer's particular purpose. The customer is responsible for the appropriate, safe and legal use, processing and handling of our products.

No liability can be accepted in respect of the use of any Borealis product in conjunction with any other products and/or materials. The information contained herein relates exclusively to our products when not used in conjunction with any other material unless as specifically provided for in the test methods stated above.

**BOREALIS**